

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/31/05	

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Contacts color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min @ 500 VDC

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant

Positions: 4 thru 80

A = .079 [2.00] x No. of Positions per Row

B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		HOLDS	
.X	± .10	ØXX	± .10		
.XX	± .020	ØXXX	± .015		
.XXX	± .015	ØXXX	± .010		
APPROVALS		DATE			
DRAWN	SS	3/31/05			
CHECKED					
APPROVED					
		TITLE		SIZE	
		.079 [2.00] DUAL ROW PIN HEADER		PART NO.	
		RIGHT ANGLE, GOLD PLATED		2PH2R-XX-UA	
		REF:		SCALE: NTS	
				SHEET 1 OF 1	

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

REV.

REV.

REV.

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2PH2R-80-UA](#) [2PH2R-08-UA](#) [2PH2R-12-UA](#) [2PH2R-10-UA](#) [2PH2R-04-UA](#) [2PH2R-14-UA](#) [2PH2R-18-UA](#) [2PH2R-02-UA](#) [2PH2R-16-UA](#) [2PH2R-06-UA](#) [2PH2R-20-UA](#)