


Rev	AWO #	Description	Date	Appr
-		RELEASED	5/27/05	
A		CHANGED TERMINALS	9/02/09	
B		CHANGED TERMINALS	5/06/11	

APPROVED: _____
DATE: _____ TITLE: _____



Positions: 02 thru 80
A = .079 [2.00] x No. of Positions per Row
B = .079 [2.00] x No. of Spaces

SPECIFICATIONS:
Material:
Insulator: Nylon, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating:
Gold flash over Nickel underplate overall
Electrical:
Current rating: 1 Amp max.
Contact resistance: 20 mohms max. initial
Insulation resistance: 5,000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

079 x .079 DUAL ROW RECEPTACLE STRIP
.169 [4.30] HEIGHT, GOLD PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015	.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS	5/27/05		CHECKED			
APPROVED							
TITLE				PART NO.			
079 x .079 DUAL ROW RECEPTACLE STRIP				2RS2-XX-G			
.169 [4.30] HEIGHT, GOLD PLATED				REV. B			
REF: S00059T				SCALE: NTS			
SHEET 1 OF 1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2RS2-20-G](#) [2RS2-12-G](#) [2RS2-02-G](#) [2RS2-04-G](#) [2RS2-34-G](#) [2RS2-06-G](#) [2RS2-16-G](#) [2RS2-10-G](#) [2RS2-08-G](#)