





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/7/05	
A		REVISED DIM.	3/2/12	



**SPECIFICATIONS:**

Material: Nylon46, rated UL 94V-0  
 Insulator color: White  
 Contacts: Brass  
 Plating: Tin over Copper underplate overall  
 Electrical:  
 Operating voltage: 100 VAC max  
 Current rating: 2 Amps max  
 Contact resistance: 10 mohms max  
 Dielectric withstanding voltage: 800 VAC for 1 minute  
 Temperature Rating: -25°C to +85°C  
 Environmental:  
 Halogen & Lead free, RoHS compliant

Positions: 2 thru 16  
 A = .079 [2.00] x No. of Positions + .153 [3.90]  
 B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES HOLEES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS \_\_\_\_\_ DATE \_\_\_\_\_

**ADAM TECH**  
 909 Railway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .079 [2.00] SHROUDED HEADER, VERTICAL, SURFACE MOUNT

DRAWN	SS	4/7/05
CHECKED		
APPROVED		

SIZE	PART NO.	REV.
X	2SH-C-XX-TS-SMT	A
REF:	S00123T	SCALE: NTS
		SHEET 1 OF 1



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2SH-C-02-TS-SMT](#) [2SH-C-03-TS-SMT](#) [2SH-C-04-TS-SMT](#) [2SH-C-06-TS-SMT](#) [2SH-C-09-TS-SMT](#) [2SH-C-10-TS-SMT](#)  
[2SH-C-08-TS-SMT](#) [2SH-C-05-TS-SMT](#) [2SH-C-07-TS-SMT](#)