





DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/9/11	



PACKAGED ON TAPE & REEL

Positions: 2 thru 16

A =	0.79	[2.00]	x No. of Positions +	.153	[3.90]
B =	0.79	[2.00]	x No. of Spaces		
C =	0.79	[2.00]	x No. of Positions +	.024	[0.60]

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 2 Amps max

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to $+85^{\circ}\text{C}$

Environmental:

Lead free, RoHS compliant.



<p>UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010</p>			
APPROVALS		DATE	
DRAWN	AY	8/5/11	
CHECKED	CC	8/9/11	
APPROVED			
<p>ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710</p>			
<p>TITLE .079 [2.00] SHROUDED HEADER, WITH CAP VERTICAL, SURFACE MOUNT</p>			
SIZE	PART NO.	REV.	
X	2SH-C-XX-TS-SMT-PP-T/R	.	
REF:	\$00015T	SCALE:	NTS SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2SH-C-12-TS-SMT-PP-T/R](#) [2SH-C-03-TS-SMT-PP-T/R](#) [2SH-C-14-TS-SMT-PP-T/R](#) [2SH-C-05-TS-SMT-PP-T/R](#)
[2SH-C-11-TS-SMT-PP-T/R](#) [2SH-C-04-TS-SMT-PP-T/R](#) [2SH-C-07-TS-SMT-PP-T/R](#) [2SH-C-15-TS-SMT-PP-T/R](#) [2SH-](#)
[C-09-TS-SMT-PP-T/R](#) [2SH-C-10-TS-SMT-PP-T/R](#) [2SH-C-02-TS-SMT-PP-T/R](#) [2SH-C-06-TS-SMT-PP-T/R](#) [2SH-C-13-](#)
[TS-SMT-PP-T/R](#) [2SH-C-08-TS-SMT-PP-T/R](#) [2SH-C-16-TS-SMT-PP-T/R](#)