







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/24/16	



SPECIFICATIONS:

Material:
Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
Insulator color: Black
Pin: Brass, Tin plated
Spring piece: Stainless Steel, Tin plated
Curve Piece: Brass, Tin plated
Electrical:
Rating: DC 30V, 1.0A
Contact resistance: 30 mohms max.
Insulation resistance: 100 Mohms min @250 VDC.
Dielectric withstanding voltage: 500 VAC
Environmental:
Lead free, RoHS compliant



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DATE			DC POWER JACK, 1.00mm, 1.30mm CENTER PIN		
DRAWN	AY	11/24/16	SIZE	PART NO.	REV.
CHECKED	AC	11/24/16	X	ADC-029S-X-HT-T/R	-
APPROVED			REF:	S00102C	SCALE: NTS
			SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ADC-029S-4-HT-T/R](#)