






APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/18/11	
A		UPDATED SPEC.	11/16/18	HR/AC1



DC MATE PLUG



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:
 Insulator: PA9T, rated UL 94V-0
 Insulator color: Black
 Center Pin: Bronze
 Contacts: Copper Alloy
 Hook: Stainless Steel
 Plating:
 Silver over Copper underplate overall
 Electrical:
 Rating: 15VDC, 2A
 Contact resistance: 30 mohms max.
 Insulation resistance: 100 Mohms min. @ 250 VDC
 Dielectric withstanding voltage: 500 VAC
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710
APPROVALS DRAWN TW CHECKED AY APPROVED			DATE 11/18/11 11/18/11		
SIZE X REF: S00002C			PART NO. ADC-098-8 SCALE: NTS		REV. A SHEET 1 OF 1

TITLE
 DC POWER JACK, 0.65mm CENTER PIN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ADC-098-8](#)