


APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/26/16	



# SPECIFICATIONS:

Material:  
 Outer Tube: Brass  
 Center Pin: Brass  
 Dielectric: ABS

Electrical:  
 Operating voltage: 12 VDC  
 Current rating: 2 Amps

Contact resistance: 30 mohms max  
 Insulation resistance: 100 Mohms min @ 500 VDC  
 Dielectric withstanding voltage: 500 VAC, 0.5mA for 1 minute

Environmental:  
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010			<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS DRAWN AY 4/26/16 CHECKED MY 4/26/16 APPROVED			TITLE <b>DC PLUG 5.5X2.5X22.5MM</b>	
SIZE <b>X</b>			PART NO. <b>ADP-.098/.217/.689-M</b>	REV. <b>-</b>
REF: S00118C			SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ADP-098-217-689-M](#)