





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	



P.C.B LAYOUT



SPECIFICATIONS:

Material:  
 Insulator: PA6T+30%GF, rated UL 94V-0  
 Insulator color: Black  
 Contacts: Brass  
 Plating:  
 Tin over Nickel underplate overall  
 Electrical:  
 Current rating: 3 Amp  
 Contact resistance: 20 mohms max  
 Insulation resistance: 1,000 Mohms min  
 Dielectric withstanding voltage: 500 VAC  
 Temperature Rating:  
 -40°C to +105°C  
 Environmental:  
 Lead free, RoHS compliant



<div>UNLESS OTHERWISE SPECIFIED</div> <div>ALL DIMENSIONS ARE MILLIMETERS</div> <div>TOLERANCES: EXCEPT AS NOTED</div> <div>MMANGLE</div> <div>X.X ± 0.25 ± 3°</div> <div>X.XX ± 0.20</div> <div>X.XXX ± 0.10</div>		<div>ADAM TECH</div> <div>INTERCONNECTS</div> <div>909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710</div>		
APPROVALS		TITLE		
DATE		2.54 PITCH PIN HEADER, 1*6 PIN, RIGHT ANGLE		
DRAWN	AY			11/27/18
CHECKED	AC			11/27/18
APPROVED				
		SIZE	PART NO.	REV
		X	ADT-AMP1151106S3BR149E2	-
REF: S00111C		SCALE: NTS		SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ADT-AMP1151106S3BR149E2](#)