



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	



SPECIFICATIONS:

Material:
 Insulator: PA6T, rated UL 94V-0
 Insulator color: Black
 Contacts: CuZn30 H140
 Plating:
 Matte Tin over Nickel underplate overall
 Electrical:
 Contact resistance: 20 mohms max
 Insulation resistance: 10G ohms min
 Dielectric withstanding voltage: 1000V/60S
 Temperature Rating:
 Operating temperature: -40°C to +125°C
 Environmental:
 Lead free, RoHS compliant



<div>UNLESS OTHERWISE SPECIFIED</div> <div>ALL DIMENSIONS ARE MILLIMETERS</div> <div>TOLERANCES: EXCEPT AS NOTED</div> <div>MMANGLE</div> <div>X.X ± 0.30 ± 3°</div> <div>X.XX ± 0.25</div> <div>X.XXX ± 0.10</div>		<div>ADAM TECH</div> <div>INTERCONNECTS</div>		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710					
				TITLE					
		APPROVALS		DATE		2.54 PITCH PIN HEADER, 1*4 PIN, STRAIGHT			
		DRAWN	AY	11/27/18					
CHECKED	AC	11/27/18							
APPROVED				SIZE X		PART NO. ADT-AMP1251104S2BS192A1		REV -	
				REF: S00111C		SCALE: NTS		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ADT-AMP1251104S2BS192A1](#)