




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	



SPECIFICATIONS:

Material:
 Insulator: PA6T+30%GF, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Plating:
 Matte Tin over Nickel underplate overall
 Electrical:
 Current rating: 3 Amp
 Contact resistance: 20 mohms max
 Insulation resistance: 1,000 Mohms min
 Dielectric withstanding voltage: 500 VAC
 Temperature Rating:
 -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



<div>UNLESS OTHERWISE SPECIFIED</div> <div>ALL DIMENSIONS ARE MILLIMETERS</div> <div>TOLERANCES: EXCEPT AS NOTED</div> <div>MMANGLE</div> <div>X.X ± 0.25 ± 3°</div> <div>X.XX ± 0.20</div> <div>X.XXX ± 0.10</div>		<div>ADAM</div> <div>TECH</div> <div>INTERCONNECTS</div>		<div>909 Rahway Avenue,</div> <div>Union, NJ 07083</div> <div>Phone: 908-687-5000</div> <div>Fax: 908-687-5710</div>		
		TITLE				
		2.54 PITCH PIN HEADER, 1*6 PIN, STRAIGHT				
		SIZE		PART NO.		REV.
		X		ADT-AMP1251106S4BS165A1		-
APPROVALS		DATE				
DRAWN	AY	11/27/18				
CHECKED	AC	11/27/18				
APPROVED						
REF:		S00111C		SCALE:	NTS	
				SHEET	1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ADT-AMP1251106S4BS165A1](#)