


APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/15/18	
A		UPDATE DIM.	7/25/19	AY/LW
B		UPDATE DIM.	10/28/21	WX/RC



6	CONNECTOR	SMA ST. PLUG REVERSE
5	CABLE	RG178 50Ω
4	RIVET	PDM;BLACK
3	BOTTOM BASE	PBT;BLACK
2	UPPER BASE	PC;BLACK
1	ANTENNA CAP	TPE;BLACK
ITEM	PART NAME	MATERIAL

SPECIFICATION

ELECTICAL PROPERTIES

FREQUENCY RANGE: 2.4~2.5/4.9~5.8 GHz

IMPEDANCE: 50Ω

VSWR: 1.92:1MAX

RETURN LOSS: -10dB MAX

RADIATION: OMNI-DIRECTIONAL

GAIN: 2.0dBi

POLARIZATION: LINEAR VERTICAL

ADMITTED POWER: 1W

PHYSICAL PROPERTIES

ANTENNA COVER: TPE

ANTENNA BASE: PC

ANTENNA: PBT

COLOR: BLACK

CONNECTOR: SMA ST. PR

OPERATING TEMPERATURE: -40~+80

STORAGE TEMPERATURE: -45~+85

ENVIRONMENTAL:

LEAD FREE, ROHS COMPLIANT



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	MM
X	± 0.50
X.X	± 0.20
X.XX	± 0.10

DRAWN	AY	11/15/18
CHECKED	AC	11/15/18
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE				
WLAN EXTERNAL ANTENNA				
SIZE	PART NO.			REV.
X	ANT-DK-DB1DI-2AB(C)-			B
REF:	S00111C	SCALE:	NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ANT-DK-DB1DI-2AB\(C\)-](#)