

6

5

4

3




2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/11/10	

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy, Tin plated.

Electrical:

Rated Voltage & Current: DC 12V, 2A max; AC100V, 1A max.

Contact resistance: 30 mohms max.

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 235°C for 5 sec.



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

3.5MM STEREO PHONE JACK, 3PIN

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
				.X				Ø.X			
				.XX				Ø.XX			
				.XXX				Ø.XXX			
APPROVALS				DATE				DATE			
DRAWN	DR	5/11/10									
CHECKED											
APPROVED											
TITLE				SIZE				PART NO.			
3.5MM STEREO PHONE JACK, 3PIN				X				ASL-125-3			
REF: S00095T				SCALE: NTS				SHEET 1 OF 1			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[ASJ-137-A-T/R](#) [ASJ-125-3](#)