
	6	5	4	3			2		1		
			•		Rev	AWO #	Description		Date	Appr	
	APPROVED:				-		RELEASED		6/9/17		
	DATE:	TITLE:			А		ADDED PAGE.2		3/4/21	WX/AC	
					В		UPDATE DRAWIN	G	3/9/21	LH/AC	
					С		ADDED SPEC.		8/5/21	LH/AC	
D					D		ADDED SPEC.		11/5/21	WX/AC	D
					E		ADDED PAGE3		3/15/24	WX/RC	
				-							
	ATHT-K3081	I	11.693 [297.00]								
	1. ATHT - 515 🛛 🖄										
	Quick Interchangeable Ratchetcri	imper						- <u>_</u>	+		
	2. ATHT - 206 Cable Cutter										
с	Coax cable cutter sizes:										
	1.24mm(AWG28)41" [10.50mm]			0							
	3. ATHT - 332)	EO .039 .100	.151			С
	Coax cable diameter range:	Blade Coaxial Cable Stripper									
	RG58 (3C): .195"±.008" [4.95±0.2mm]										
	RG59/RG62(4C):.242"±.008" [6.15±0.2mm]										
	RG6 (5C): .276"±.008" [7.0±0.2mm RG174 : .100"±.008" [2.54±0.2mm			т.		(<u> </u>					
	The above information is for referen								ا 7.756		—
	It must be based on the actual cutti	ng line				2			[197.00]		
	on the coax cable diameter range for	or the cable stripper.									
	4. ATHT - 3A4 Dimension 255" / 187" / 068" / 2	nension .255" /.187" /.068" /.213"						_			
	6.48 / 4.76 / 1.73 / 5.41 mm										
в	Cable type RG 58, 59, 62, 174									в	
5	Cable type RG 58, 59, 62, 174 . ATHT - 3C Dimension .256" /.319" /.068" /.213"										
	6.50 / 8.10 / 1.73 / 5.41 mm						A49 .100 _213				
	Cable type RG 58, 59, 62, 6						8				
	6. ATHT - 3G						/				
	Dimension .043"/.068"/.100"/. 1 09 / 1 73 / 2 54 / 3	137" / 213" / 255" 3.48 / 5.41 / 6.48 mm							•		
	Cable type RG 58, 59, 62, 174										
	7. ATHT - 3J										
	Dimension .042" /.068" /.078" /.1			LINLESS OTHE			IONS	00		20110	
	1.07 / 1.73 / 1.98 / 3.25 / 3.84 / 4.52 mm Cable type RG 174, 179, Beiden 8218 8. ATHT- 3K Dimension .100" / .128" / .429"				HERWISE SPECIFIED ALL DIMENSIONS $[MM]$. TOLERANCES: EXCEPT AS NOTED INCHES HOLES \pm .10 ØX \pm .10 \leftarrow ±.020 ØXX \pm .015 $(X \pm .015)$ ØXXX \pm .010				Phone: 908-687-500		
								rli Ph		5000	
Α								Fa	ax: 908-687-57	10	Α
	2.54 / 3.25 / 10.90 n Cable type RG 8, 11, 174, 179, 3	2.54 / 3.25 / 10.90 mm e BG 8 11 174 179 213				6/		CHANGEARI E	EABLE RATCHET CRIMP TOO		1
9. ATHT-311 CHECKED CK 6/9/17 K							ND DIES FOR R				
	Dimension .028" / .039" / .047"/.1						SIZE PART NO.		1	REV.	
	.071/ .099 / 1.19/ 2. Cable type RG 174, 178, 179, 1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH				ATHT-K3081 E				
	6	5	4	3			2	JUALE:	1	- 0 3	1
	v	I v	т Т	v v			-	1	•		



	6	5	4	3			2		1		
		-			Rev A	WO #	Description		Date	Appr]
						S	EE SHT 1 OF 3 FOR RE	VISION			4
	DATE:	TITLE:									
D			ATHT-3J								D
			<u>AIIII-JJ</u>								
		7									
		I									
		.433 .236 [11.00] [6.00]									
				y							
		<u>'</u>									
С											C
			5315.70	#1	Edge-	-to-edte diam	eter of diamond	hole:			
				TT #2	<u> </u>	42±0.04" (1.0 -to-edge_diam	neter of hex hole:				
				111	#3.0	68±0.04" (1.7 78±0.04" (1.9	'3±0.10mm) 98±0.10mm)				
				3J H #3	5	28±0.04" (3.2 51±0.04" (3.8	25±0.10mm) 34±0.10mm)				
			\sim $ \cdot\rangle$ $ \cdot\rangle$		#6 .1	78±0.04" (4.5	2±0.10mm)				
		1.417 [36.00]		() +#≠	ŀ						
В				#5)						в
					、 、						
				#6)						
			1.417 [36.00] REF	- 							Γ
											1
				ARE INCHES [-	EXCEPT AS NOTED		909 F	Rahway Ave n, NJ 07083		
				.X .XX	± .10 Ø.X ± .020 Ø.XX	HOLES ±.10 ±.015		Phone	e: 908-687-5	5000	
A				.XXX DRAWN	± .015 Ø.XXX	(±.010 6/9/17	TITLE		908-687-571		^
				CHECKED	ск	6/9/17		CHANGEABLE RA			
						N THAT IS PROPRIETAR)	SIZE PART NO.	ATHT-K3081		REV.	1
				AND SHOULD NO PERMISSION FRO	T BE USED WITHOUT F	PRIOR WRITTEN	REF: -	SCALE: NT	S SHEET	Е Т 3 ОГ 3	5
	6	5	4	3			2		1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Adam Tech:

ATHT-3C ATHT-K3081 ATHT-3A4 ATHT-3G ATHT-3K ATHT-3J ATHT-3T1 ATHT-515 ATHT-332 ATHT-206