

6

5

4

3

2

1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev

AWO #




Description

Date

Appr

RELEASED

3/25/20



RECOMMENDED PCB LAYOUT

## SPECIFICATIONS:

Material:

Housing: Hi-temp thermoplastic, Color: Black

Contact: Phosphor Bronze, Gold plated

Electrical:

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Megaohms ohms min

Dielectric Voltage: 500 VAC one sec level

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MILLIMETERS  
TOLERANCES: EXCEPT AS NOTED  
MM ANGLE

X ± 0.30 X ± 1°  
X.X ± 0.25 X.X ± 0.5°  
X.XX ± 0.20  
X.XXX ± 0.10

**ADAM**  
**TECH**  
INTERCONNECTS

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE

BATTERY HOLDER, FOR TWO "AAA" CELLS, SMT

APPROVALS

DATE

DRAWN

LH

3/25/20

CHECKED

MY

3/25/20

APPROVED

SIZE

X

PART NO.

BH-102B-5

REV.

-

REF: S00136C

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-102B-5](#)