






APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/12/20	



# SPECIFICATIONS:

## Material:

Housing: PBT, rated UL94V-0, Color: Black

Contact: Mn Steel, Nickel plated

## Electrical:

Contact resistance: 30 Milliohms max

Insulation resistance: 1,000 Megohms ohms min

Dielectric Voltage: 500 VAC @ sea level

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MILLIMETERS  
TOLERANCES: EXCEPT AS NOTED  
MM ANGLE  
X  $\pm 0.30$  X  $\pm 1^\circ$   
X.X  $\pm 0.25$  X.X  $\pm 0.5^\circ$   
X.XX  $\pm 0.20$   
X.XXX  $\pm 0.10$

APPROVALS		DATE
DRAWN	LH	3/12/20
CHECKED	MY	3/12/20
APPROVED		

**ADAM**  
**TECH**  
INTERCONNECTS

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE BATTERY HOLDER, PCB THRU HOLE  
FOR 2032, DIP TYPE

SIZE X	PART NO. BH-124A-1	REV. -
REF: S00136C	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-124A-1](#)