

6

5

4

3


2

1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/15	



## SPECIFICATIONS:

## Material:

Housing: PBT, rated UL94V-0, Color: Black

Contact: Brass, Tin plated

## Electrical:

Contact resistance: 30 Milliohms max

Insulation resistance: 1000 Mega ohms min

Dielectric Voltage: 500V AC one sec level

Temperature Rating:

Operating temperature: -25°C to +85°C.

## Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	AY	5/28/15
CHECKED	OC	5/28/15
APPROVED		

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
BATTERY HOLDER, PCB THRU HOLE  
FOR 2032

SIZE	PART NO.	REV.
X	BH-25C-1	-
REF:	S00136C	SCALE: NTS
SHEET 1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-25C-1](#)