

6

5

4

3

2

1


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/13/20	



RECOMMENDED P.C.B LAYOUT



SPECIFICATIONS:

Material:

Housing: Hi-Temp Thermoplastic, rated UL94V-0

Housing Color: White

Contact: Phosphor Bronze, Gold Plated

Electrical:

Contact resistance: 30 Milliohms max

Insulation resistance: 1,000 Megaohms ohms min

Dielectric Voltage: 500 VAC one sec level

Temperature Rating:

Operating temperature: -25°C to +85°C.

Environmental:

Lead free, RoHS compliant

RoHS
COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
MM ANGLE
X ± 0.30 X ± 1°
X.X ± 0.25 X.X ± 0.5°
X.XX ± 0.20
X.XXX ± 0.10

APPROVALS		DATE
DRAWN	LH	3/13/20
CHECKED	MY	3/13/20
APPROVED		
SIZE	PART NO.	REV.
X	BH-27A-5-G-WT	-
REF: S00136C	SCALE: NTS	SHEET 1 OF 1

ADAM
TECH
INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

BATTERY COIN CELL HOLDER, CR 2032
WHITE COLOR, SMT TYPE, GOLD PLATED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-27A-5-G-WT](#)