



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/24/15	



SPECIFICATIONS:

Material:
 Housing: Hi-Temp Thermoplastic, Glass reinforced rated UL94V-0
 Housing Color: White
 Contact: Phosphor Bronze
 Plating:
 Tin over Copper underplate overall
 Electrical:
 Contact resistance: 30 Milliohms max
 Insulation resistance: 1,000 Megaohms ohms min
 Dielectric Voltage: 500 VAC one sec level
 Temperature Rating:
 Operating temperature: -25°C to +85°C.
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			<div>ADAM TECH</div> <div>909 Rahway Avenue, Union, NJ 07083</div> <div>Phone: 908-687-5000 Fax: 908-687-5710</div>		
APPROVALS			TITLE		
DATE			BATTERY COIN CELL HOLDER, CR 2032		
DRAWN			WHITE COLOR		
HR					
6/24/15					
CHECKED			SIZE		
LW			X		
6/24/15			PART NO.		
APPROVED			BH-27A-5-WT		
			REV		
			-		
			REF: S00136C		
			SCALE: NTS		
			SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-27A-5-WT](#)