



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/15	
A		UPDATED DRAWING	8/9/16	AY/LW



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:
Housing: PBT, rated UL94V-0, Color: Black
Contact: Mn Steel, Nickel plated
Electrical:
Contact resistance: 30 Milliohms max
Insulation resistance: 1000 Mega ohms min
Dielectric Voltage: 500V AC one sec level
Temperature Rating:
Operating temperature: -25°C to +85°C.
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES		HOLES		TITLE COIN CELL BATTER HOLDER, CR 2477, PCB MOUNT			
.X	± .10	Ø.X	± .10	SIZE	PART NO.		REV.
.XX	± .020	Ø.XX	± .015	X	BH-32C-1		A
.XXX	± .015	Ø.XXX	± .010	REF:	S00136C	SCALE: NTS	SHEET 1 OF 1
APPROVALS				DATE			
DRAWN		AY		5/28/15			
CHECKED		OC		5/28/15			
APPROVED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-32C-1](#)