





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/11/17	
A		UPDATE DRAWING	4/24/20	OW/EY



RECOMMENDED P.C.B LAYOUT



SPECIFICATIONS:

Material:

Insulator: PBT, Glass Fibre rated UL 94V-0

Insulator color: Black

Contacts: Brass, Tin plated

Electrical:

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric voltage: 500 VAC on Sec level

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
MM ANGLES
X ± 0.30 X ± 1°
X.X ± 0.25 X.X ± 0.5°
X.XX ± 0.20
X.XXX ± 0.10

APPROVALS		DATE
DRAWN	AY	1/11/17
CHECKED	CH	1/11/17
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
BATTERY HOLDER, PCB TERMINALS FOR ONE "COIN" CELL, CR 2330			
SIZE X	PART NO. BH-35A-1	REV. A	
REF: S00136C	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-35A-1](#)