





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/11/16	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Housing: Hi-Temp Thermoplastic (PPS) rated UL94V-0, Color: Brown

Contact: Phosphor Bronze, Gold plated

Electrical:

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric Voltage: 500 VAC one sec level

Temperature Rating:

Operating temperature: -25°C to +85°C.

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X	± .10	Ø.X	± .10		
.XX	± .020	Ø.XX	± .015	TITLE BATTERY HOLDER, SURFACE MOUNT, FOR CR1220, BROWN COLOR	
.XXX	± .015	Ø.XXX	± .010		
APPROVALS		DATE		SIZE	PART NO.
DRAWN	AY	8/11/16		X	BH-44C-5
CHECKED	LW	8/11/16		REF: S00136C	SCALE: NTS
APPROVED				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-44C-5](#)