

6

5

4

3

2



1

APPROVED: \_\_\_\_\_



DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/30/15	
A		UPDATE DRAWING	1/15/19	AY/YC
B		UPDATE DRAWING	4/9/20	LH/OC

D




C



RECOMMENDED P.C.B. LAYOUT

B



## SPECIFICATIONS:

## Material:

Housing: Hi-Temp Thermoplastic, rated UL94V-0, Color: White

Contact: Phosphor Bronze, Gold plated

## Electrical:

Contact resistance: 30 Milliohms max

Insulation resistance: 1,000 Megaohms ohms min

Dielectric Voltage: 500 VAC @ sea level

Temperature Rating:

Operating temperature: -25°C to +85°C

## Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE MILLIMETERS  
 TOLERANCES: EXCEPT AS NOTED  
 MM ANGLE  
 X ± 0.30 X ± 1°  
 X.X ± 0.25 X.X ± 0.5°  
 X.XX ± 0.20  
 X.XXX ± 0.10

APPROVALS		DATE
DRAWN	AY	4/9/20
CHECKED	NC	4/9/20
APPROVED		
SIZE	PART NO.	REV.
X	BH-49A-5	B
REF: S00136C	SCALE: NTS	SHEET 1 OF 1

**ADAM**  
**TECH**  
**INTERCONNECTS** 909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

COIN CELL BATTERY HOLDER FOR  
 CELL CR2032, SMT TYPE

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-49A-5](#)