






APPROVED: _____
 DATE: _____ TITLE: _____

| Rev | AWO # | Description | Date | Appr |
|-----|-------|-------------|---------|------|
| - | | RELEASED | 3/13/20 | |



RECOMMENDED P.C.B LAYOUT



SPECIFICATIONS:

Material:
 Housing: Hi-Temp Thermoplastic, rated UL94V-0, Color: Black
 Contact: Phosphor Bronze, Tin plated
 Electrical:
 Contact resistance: 30 Milliohms max
 Insulation resistance: 1,000 Megaohms ohms min
 Dielectric Voltage: 500 VAC @ sea level
 Temperature Rating:
 Operating temperature: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant



| | | | |
|---|------------|---------|--|
| UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED | | | |
| MM | ANGLE | | |
| X ± 0.30 | X ± 1° | | |
| X.X ± 0.25 | X.X ± 0.5° | | |
| X.XX ± 0.20 | | | |
| X.XXX ± 0.10 | | | |
| APPROVALS | | DATE | |
| DRAWN | LH | 3/13/20 | |
| CHECKED | MY | 3/13/20 | |
| APPROVED | | | |

ADAM TECH
 INTERCONNECTS
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

| | | | |
|--|---------------------------|--------------|--|
| TITLE COIN CELL BATTERY HOLDER FOR CELL CR2032, SMT TYPE, COLOR: BLACK | | | |
| SIZE X | PART NO. BH-49A-5-T-BK | REV. - | |
| REF: S00136C | SCALE: NTS | SHEET 1 OF 1 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-49A-5-T-BK](#)