


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/11/16	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:
 Housing: Hi-Temp Thermoplastic (LCP), rated UL94V-0, Color: White
 Contact: Phosphor Bronze, Tin plated
 Electrical:
 Contact resistance: 30 mohms max
 Insulation resistance: 1,000 Mohms min
 Dielectric Voltage: 500 VAC one sec level
 Temperature Rating:
 Operating temperature: -25°C to +85°C.
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			<div>ADAM TECH</div> <div>909 Rahway Avenue, Union, NJ 07083</div> <div>Phone: 908-687-5000 Fax: 908-687-5710</div>			
.X	± .10	Ø.X				±.10
.XX	± .020	Ø.XX				± .015
.XXX	± .015	Ø.XXX				± .010
APPROVALS		DATE		TITLE BATTERY HOLDER, PCB THRU HOLE FOR CR2032, WHITE COLOR		
DRAWN	HR	8/11/16				
CHECKED	LW	8/11/16				
APPROVED						
SIZE		PART NO.		REV.		
X		BH-49C-1		-		
REF: S00136C		SCALE: NTS		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-49C-1](#)