



Rev	AWO #	Description	Date	Appr
-		RELEASED	2/9/12	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material: Insulator: PBT, glass fiber rated UL 94V-0
 Insulator color: Black
 Contacts: Phosphor Bronze
 Electrical: Current rating: 30 Milliamps max
 Insulation Resistance: 1000 Mega ohms min
 Dielectric Withstands Voltage: 750V AC for 1 min.
 Temperature Rating: Operating temperature: -55°C to +85°C
 Environmental: Lead free, RoHS compliant
 Recommended soldering temp: 235°C for 5 seconds

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

2PIN BATTERY HOLDERS, SMT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES	HILES	HILES	HILES	2PIN BATTERY HOLDERS, SMT			
.X ± .10	ØX ± .10	ØX ± .10	ØX ± .10				
.XX ± .020	ØXX ± .015	ØXX ± .015	ØXX ± .015				
.XXX ± .015	ØXXX ± .010	ØXXX ± .010	ØXXX ± .010				
APPROVALS				DATE			
DRAWN	AY			2/9/12			
CHECKED	AH			2/9/12			
APPROVED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-55-5](#)