




Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/15	

APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material: Insulator: PBT, rated UL 94V-0  
Insulator color: Black  
Contacts: Brass, Tin plated  
Electrical: Contact resistance: 30 mohms max  
Insulation resistance: 1,000 Mohms min  
Dielectric withstanding voltage: 500 VAC one sec level  
Temperature Rating: Operating temperature: -25°C to +85°C  
Environmental: Lead free, RoHS compliant



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

BATTERY HOLDER, PCB THRU HOLE, FOR 2032

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	HR		5/28/15				
CHECKED	OC		5/28/15				
APPROVED							
TITLE				REV.			
BATTERY HOLDER, PCB THRU HOLE, FOR 2032				-			
SIZE				PART NO.			
X				BH-80A-1			
REF: S00136C				SCALE: NTS			
				SHEET 1 OF 1			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-80A-1](#)