





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/11/20	



PART NO.	MATERIAL
BH-82-1-1A	PBT, BLACK
BH-82-1-1B	PA66, BLACK
BH-82-1-2A	PPA, BROWN
BH-82-1-2B	PPA, BLACK
BH-82-1-3A	PPS, BROWN
BH-82-1-3B	PPS, BLACK
BH-82-1-4A	LCP, WHITE
BH-82-1-4B	LCP, BLACK

SPECIFICATIONS:

Material:

Housing: (See chart)

Housing Color: (See chart)

Contact: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Contact resistance: 30 Milliohms max

Insulation resistance: 1,000 Megaohms ohms min

Dielectric Voltage: 500 VAC one sec level

Temperature Rating:

Operating temperature: -25°C to +85°C.

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE MILLIMETERS
 TOLERANCES: EXCEPT AS NOTED
 MM ANGLE
 X ± 0.30 X ± 1°
 X.X ± 0.25 X.X ± 0.5°
 X.XX ± 0.20
 X.XXX ± 0.10

APPROVALS		DATE
DRAWN	LH	3/11/20
CHECKED	OC	3/11/20
APPROVED		

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE			
BATTERY HOLDER, DIP TYPE, FOR TWO AG13 / LR44 COIN CELL			
SIZE	PART NO.	REV.	
X	BH-82-1-XX	-	
REF: S00136C	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-82-1-2B](#)