






APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/17/20	



RECOMMENDED PCB LAYOUT

#### SPECIFICATIONS:

Material:  
 Housing: Hi-Temp Thermoplastic, rated UL94V-0, Color: White  
 Contact: Phosphor Bronze, Gold plated  
 Electrical:  
 Contact resistance: 30 Milliohms max  
 Insulation resistance: 1,000 Megohms ohms min  
 Dielectric Voltage: 500 VAC @ sea level  
 Temperature Rating:  
 Operating temperature: -25°C to +85°C  
 Environmental:  
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE MILLIMETERS  
 TOLERANCES: EXCEPT AS NOTED  
 MM ANGLE  
 X ± 0.30 X ± 1°  
 X.X ± 0.25 X.X ± 0.5°  
 X.XX ± 0.20  
 X.XXX ± 0.10

**ADAM**  
**TECH**  
 INTERCONNECTS

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	LH	3/17/20
CHECKED	MY	3/17/20
APPROVED		

TITLE BATTERY HOLDER, PCB THRU HOLE  
 FOR 2032, SMT TYPE

SIZE X	PART NO. BH-92A-5	REV. -
REF: S00136C	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BH-92A-5](#)