





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/28/04	



SPECIFICATION:

Material:

Insulator: PBT, glass reinforced, rated UL-94V-0

Insulator color: Black

Contacts: Brass

Contact Plating:

Gold Flash over Nickel underplate overall

Electrical:

Current rating: 1 Amps max.

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C TO +105°C

Environmental:

Lead free, RoHS compliant.



A = .100 [2.54] X No. of Positions /2 + .300 [7.60]

B = .100 [2.54] X No. of Positions /2 + .200 [5.08]

C = .100 [2.54] X No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE BOX HEADER, RIGHT ANGLE PCB MOUNT, 2 ROW .100 PITCH, GOLD FLASH PLATED		
DRAWN	SS	7/28/04	SIZE X	PART NO. BHR-XX-HUA	REV. -
CHECKED			REF:	SCALE: NTS	SHEET 1 OF 1
APPROVED					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

<u>BHR-34-HUA</u>	<u>BHR-16-HUA</u>	<u>BHR-26-HUA</u>	<u>BHR-20-HUA</u>	<u>BHR-40-HUA</u>	<u>BHR-50-HUA</u>	<u>BHR-10-HUA</u>	<u>BHR-12-HUA</u>
<u>BHR-64-HUA</u>	<u>BHR-24-HUA</u>	<u>BHR-08-HUA</u>	<u>BHR-14-HUA</u>	<u>BHR-60-HUA</u>	<u>BHR-06-HUA</u>	<u>BHR-30-HUA</u>	<u>BHR-44-HUA</u>