





Rev	AWO #	Description	Date	Appr
-		RELEASED	3/25/05	

APPROVED: _____
DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: PBT, Glass filled, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max.

Current rating: 3 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5,000 Mohms min.

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant

Recommended soldering temp: 230°C for 5 seconds



Positions: 8, 10, 14, 16, 20, 24, 26, 30, 34, 40, 44, 50, 60, 64
A = .100 [2.54] x No. of Positions/2 + .300 [7.62]
B = .100 [2.54] x No. of Spaces/2 + .200 [5.08]
C = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES
.X ± .10 ØXX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

ADAM TECH

TITLE
.100 [2.54] BOX HEADER, STRAIGHT,
TIN PLATED, STANDARD SOLDER TAIL

SIZE	PART NO.	REV.
X	BHR-XX-VTA	-
REF.	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BHR-06-VTA](#) [BHR-24-VTA](#) [BHR-10-VTA](#)