





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/04	



SPECIFICATION:

Material:

Insulator: PBT, rated UL-94V-0

Contacts: Brass

Contact Plating:

Gold Flash over Nickel underplate overall

Electrical:

Operating Voltage: 250V AC max.

Current rating: 3 Amps max.

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Dielectric withstanding voltage: 1000 VAC / minute

Mechanical:

Mating durability: 500 cycles min.

Temperature Rating:

Operating temperature: -55° TO +105°

Environmental:

Lead free, RoHS compliant.



A = .100 [2.54] X No. of Positions /2 + .300 [7.60]

B = .100 [2.54] X No. of Positions /2 + .200 [5.08]

C = .100 [2.54] X No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS		DATE
DRAWN	SS	11/16/04
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE BOX HEADER, VERTICAL PCB MOUNT,
 2 ROW .100 PITCH, GOLD FLASH PLATED

SIZE X	PART NO. BHR-XX-VUA	REV. -
REF:	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BHR-34-VUA](#) [BHR-14-VUA](#) [BHR-16-VUA](#) [BHR-20-VUA](#) [BHR-10-VUA](#) [BHR-40-VUA](#) [BHR-26-VUA](#) [BHR-50-VUA](#)
[BHR-24-VUA](#) [BHR-44-VUA](#) [BHR-64-VUA](#) [BHR-06-VUA](#) [BHR-08-VUA](#) [BHR-60-VUA](#) [BHR-30-VUA](#) [BHR-12-VUA](#)