





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/04	
A		REDRAWN	10/27/10	
B		UPDATED SPEC.	6/30/16	HR/AL



RECOMENDED PCB LAYOUT



SPECIFICATION:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator Color: Black

Metal Latch: Zinc Alloy, Nickel plated.

Contacts: Brass

Contact Plating:

Gold Flash over Nickel underplate overall

Electrical:

Current rating: 3 Amps

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 1000 VAC/DC

Temperature Rating:

Operating temperature: -40°C TO +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 06, 08, 10, 14, 16, 20, 24, 26, 30, 34, 40, 50, 60, 64

A = .100 [2.54] X No. of Positions /2 + .300 [7.62]

B = .100 [2.54] X No. of Positions /2 + .088 [2.24]

C = .100 [2.54] X No. of Positions /2 - .100 [2.54]

Above 20 Positions with "E" Profile

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	11/16/04
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE			
BOX HEADER, .100 PITCH, PCB MOUNT, 2 ROW, METAL LATCH, GOLD PLATED			
SIZE X	PART NO. BHR-XX-VUA-ML	REV. B	
REF: S00019C	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[BHR-14-VUA-ML](#) [BHR-16-VUA-ML](#) [BHR-40-VUA-ML](#) [BHR-30-VUA-ML](#) [BHR-08-VUA-ML](#) [BHR-34-VUA-ML](#) [BHR-10-VUA-ML](#) [BHR-20-VUA-ML](#) [BHR-50-VUA-ML](#) [BHR-26-VUA-ML](#) [BHR-24-VUA-ML](#)