

6

5

4

3

2

1

APPROVED: _____


DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/20/20	
A		UPDATE SPEC.	10/26/20	LH/RC
B		ADDED DIM.	1/5/21	LH/RC

P1

P2



ADAM P/N	DIM.A(MM)	DIM.A(IN)	DIM.B(MM)	DIM.B(IN)
CA-BNC-P-P-01-282L	200±2	7"	282±2	11"
CA-BNC-P-P-01-305L	223±2	8"	305±2	12"
CA-BNC-P-P-01-582L	500±3.5	19"	582±3.5	22"
CA-BNC-P-P-01-915L	833±3.5	32"	915±3.5	36"
CA-BNC-P-P-01-1000L	918±3.5	36"	1000±5	39"
CA-BNC-P-P-01-1082L	1000±5	39"	1082±5	42"
CA-BNC-P-P-01-1800L	1718±5	67"	1800±5	70"
CA-BNC-P-P-01-2082L	2000±10	78"	2082±10	81"
CA-BNC-P-P-01-3082L	3000±20	118"	3082±20	121"

SPECIFICATIONS:**Connector:**

P1= BNC Plug, Straight, Overmold Color: Black PVC

P2= BNC Plug, Straight, Overmold Color: Black PVC

Cable:

RG-58 C/U, Jacket Color: Black PVC

Electrical:Nominal Impedance: 50 ohms Δ **Electrical Test:**All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	LH	10/20/20
CHECKED	RC	10/20/20
APPROVED		

ADAM
TECH

 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

 TITLE
 CUSTOM CABLE ASSEMBLY, BNC PLUG
 TO BNC PLUG WITH RG-58 CABLE

SIZE	PART NO.	REV.
X	CA-BNC-P-P-01-XXXL	B
REF: S00092T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-BNC-P-P-01-1000L](#)