

6

5

4

3

2




1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/18	

Washer:  
Brass, GoldNut:  
Brass, Gold**SPECIFICATIONS:****Connector:**

P1= I-PEX Connector, Gold plated

P2= SMA Jack, Straight, Female pin, Gold plated

**Cable:**

Ø1.13mm Coaxial Cable, Color: Black

**Electrical:**

Impedance: 50 ohms

Frequency range: DC-6 GHz

**Electrical Test:**All Assemblies must be 100% Tested for  
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	AY	11/16/18
CHECKED	AC	11/16/18
APPROVED		

**ADAM**  
**TECH**  
**INTERCONNECTS**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
CUSTOM CABLE ASSEMBLY, IPEX PLUG  
TO SMA S/T JACK WITH OD 1.13MM CABLE

SIZE	PART NO.	REV.
X	CA#DKCA1-152L0-AJ10	-
REF: S00291T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-DKCA1-152L0-AJI0](#)