

6

5

4

3

2


1

APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/18	



SPECIFICATIONS:

P1: MMCX RF Connector, Right Angle Type, 50 ohm
P2: Stripped and Tinned.

Wire:

RF CABLE, RG316.

Electrical Test:

All assemblies must be 100% tested for shorts,
open continuity and physical appearance.

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .1	Ø.X	± .1
.XX	± .02	Ø.XX	± .01
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	AY	11/16/18
CHECKED	AC	11/16/18
APPROVED		

ADAM
TECH
INTERCONNECTS909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

RF CABLE, MMCX PLUG RIGHT ANGLE, RG-316

SIZE

X

PART NO.

CA#DKCA1-152L5-EPR-HSBL-12

REV.

-

REF: S00291T

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-DKCA1-152L5-EPR-HSBL-12](#)