



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/4/20	
A		UPDATED TITLE	1/7/22	JJ/RC



SPECIFICATIONS:

Material:

Insulator: PC, Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy, Silver plated surface

Electrical:

Current rating: 16A

Voltage rating: 120 VAC

Contact Impedance: 0.5 mohms max

Insulation resistance: 1,000 Mohms min, DC 500V

Dielectric withstanding voltage: 2,000V

Mechanical:

Mechanical life: unloaded plugged: >10,000

Insertion and Extraction Force: <80N

Temperature Rating:

Operating temperature: -30°C to +50°C

Environmental:

Waterproof grade: IP54

Lead free, RoHS compliant



ADAM TECH P/N	LENGTH
CA #EV01AT-002-3M	3,000mm ±30mm
CA #EV01AT-002-5M	5,000mm ±30mm

Charging plug: according to SAE J1772-2017 standard

Charging cable: 3x2.5mm²+1x0.5mm² (outer leather material TPE)

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED			ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
DRAWN	OW	6/4/20	TITLE CABLE ASSEMBLY EV CHARGER TYPE 1 FEMALE PLUG 16A 120V 1PHASE 2.5MM² TUV			
CHECKED	AC	6/4/20				
APPROVED						
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH			SIZE X	PART NO. CA #EV01AT-002-XM	REV. A	
			REF: -	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA #EV01AT-002-5M](#) [CA#EV01AT-002-5M](#)