




Rev	AWO #	Description	Date	Appr
-		RELEASED	10/19/15	

APPROVED: _____
DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE



ADAM P/N	L
CA-MINIDP-VGAF-3FT	36.024"±.394" [915±10mm]
CA-MINIDP-VGAF-6FT	72.047"±.787" [1830±20mm]
CA-MINIDP-VGAF-10FT	120.079"±1.181" [3050±30mm]



SPECIFICATIONS:

Connector:

P1 = High Density D-Sub Connector, Socket, 15P, VGA, W/Plastic Shell, Color: White, ABS, Surface polished, W/PCB board, W/Jackscrew

P2 = Mini Display Port Plug, W/Cap, 50P PVC

Cable:

UL20276, (32#*1P+ADM)*5C+32#*3C+28#*2C+A+B, O.D: .217" [5.5mm], Jacket Color: White

Electrical Test:

All Assemblies must be 100% Tested for

Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE CUSTOM ASSEMBLY, HIGH DENSITY D-SUB
SOCKET VGA 15P TO MINI DISPLAY PORT PLUG

SIZE	PART NO.	REV.
X	CA-MINIDP-VGAF-XFT	-

APPROVALS	DATE
DRAWN	HR
CHECKED	TW
APPROVED	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-MINIDP-VGAF-3FT](#)