


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/12/18	



SPECIFICATIONS:

Connector:

P1 = USB Type-A Male, Insulator Color: White, Contact: Gold flash plated
 Overmold Color: White, 45P PVC, Salt spray test: 48H

P2 = Circular POGO Pin connector Male, Right angle, Overmold Color: White, 45P PVC

Cable:

20AWG, 2C, O.D: .157" [4mm], Jacket Color: White, PVC 55P

Electrical:

Rated Current & Voltage: 52VDC, 3A max

Contact resistance: 50 mohms max

Electrical Test:

All Assemblies must be 100% Tested for
 Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant.



Mating with: PHR-C4777-02A-FVP-800

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED Millimeters ANGLE 0~6 ± 0.10 6~30 ± 0.20 ± 2° 30~150 ± 0.30		<div>ADAM TECH INTERCONNECTS</div> <div>909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710</div>	
APPROVALS		TITLE	
DRAWN	HR	POGO PIN CHARGING CABLE, MALE, R/A, WHT	
CHECKED	CK	POGO PIN CHARGING CABLE, MALE, R/A, WHT	
APPROVED		POGO PIN CHARGING CABLE, MALE, R/A, WHT	
		SIZE X	PART NO. CA-RA2-PHR-34113-M-WT
		REF: S00170C	SCALE: NTS
		SHEET 1	OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-RA2-PHR-34113-M-WT](#)