

6

5

4

3


2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/12/18	



USB→Wire→CONN		
Vcc_1+_red	→ 1 →	Pin
GND_4-_Black	→ 4 →	Shell

SPECIFICATIONS:

Connector:

P1 = USB Type-A Male, Insulator Color: Black, Contact: Gold flash plated

Overmold Color: Black, 45P PVC, Salt spray test: 48H

P2 = Circular POGO Pin connector Male, Straight Overmold Color: Black, 45P PVC

Cable:

22AWG, 2C, O.D: .138" [3.5mm], Jacket Color: Black, PVC 55P

Electrical:

Rated Current & Voltage: 12VDC, 3A

Contact resistance: 50 mohms max

Mechanical:

Contact force: 80±20g @ 1.10mm working stroke

Full stroke: 1.60mm

Durability: 100,000 Cycles

Electrical Test:All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

Lead free, RoHS compliant.



Mating with: PHR-C4777-02-FVP-800

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED Millimeters ANGLE 0~6 ± 0.10 6~30 ± 0.20 30~150 ± 0.30		<div>ADAM TECH INTERCONNECTS</div> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		TITLE	
DATE		POGO PIN CHARGING CABLE, MALE, STRAIGHT	
DRAWN	HR	11/12/18	
CHECKED	CK	11/12/18	
APPROVED			
SIZE	PART NO.	REV.	
X	CA-ST2-PHR-198-M	-	
REF:	S00170C	SCALE:	NTS
SHEET 1 OF 1			

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-ST2-PHR-198-M](#)