

6

5

4

3

2


1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	



PIN ASSIGNMENT			
P1		P2	
1	RED	1	
2	WHITE	2	
3	GREEN	3	
4	BLACK	4	
5	BLUE	5	
6	YELLOW	6	
7		7	
8	PURPLE	8	
9	ORANGE	9	
S	BRAID	S	

ADAM P/N	L
CA-USB3-AM/AF-3FT	36.024"±1.181" [915±30mm]
CA-USB3-AM/AF-6FT	72.047"±1.969" [1830±50mm]
CA-USB3-AM/AF-10FT	120.079"±1.969" [3050±50mm]

**SPECIFICATIONS:****Connector:**P1= USB 3.0 Connector A type Plug, Gold Flash Plated,  
Insulator Color: Blue, Overmold Color: Blue, 50P PVCP2= USB 3.0 Connector A type Socket, Gold Flash Plated,  
Insulator Color: Blue, Overmold Color: Blue, 50P PVC**Cable:**UL20276, (30#\*1P+D+A+M)\*2C+30#\*1P+26#\*2C+A+B,  
OD: .189" [4.8mm], Jacket Color Blue.**Electrical Test:**All Assemblies must be 100% Tested for  
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES.X ±.10 Ø.X ±.10  
.XX ±.020 Ø.XX ±.015  
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	HR	10/13/15
CHECKED	TW	10/13/15
APPROVED		

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
CUSTOM ASSEMBLY, USB 3.0 PLUG TYPE A  
USB 3.0 SOCKET TYPE A

SIZE	PART NO.	REV.
X	CA-USB3-AM/AF-XFT	-
REF:	S00087T	SCALE: NTS
SHEET 1 OF 1		

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-USB3-AM-AF-6FT](#)