


6		5		4		3		2		1		
APPROVED: _____							Rev	AWO #	Description		Date	Appr
							-		RELEASED		10/13/15	

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE



PIN ASSIGNMENT			
P1			P2
1	RED		1
2	WHITE		2
3	GREEN		3
4	BLACK		4
5	BLUE		5
6	YELLOW		6
7			7
8	PURPLE		8
9	ORANGE		9
S	BRAID		S

ADAM P/N	L
CA-USB3-AM/BM-3FT	36.024"±1.181" [915±30mm]
CA-USB3-AM/BM-6FT	72.047"±1.969" [1830±50mm]
CA-USB3-AM/BM-10FT	120.079"±1.969" [3050±50mm]

SPECIFICATIONS:
Connector:
P1= USB 3.0 Connector A type Plug, Gold Flash Plated,
Insulator Color: Blue, Overmold Color: Blue, 50P PVC
P2= USB 3.0 Connector B type Plug, Gold Flash Plated,
Insulator Color: Blue, Overmold Color: Blue, 50P PVC
Cable:
UL20276, (30#*1P+D+A+M)*2C+30#*1P+26#*2C+A+B,
OD: .189" [4.8mm], Jacket Color Blue
Electrical Test:
All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X ± .10	Ø.X ± .10	TITLE		CUSTOM ASSEMBLY, USB 3.0 PLUG TYPE A			
.XX ± .020	Ø.XX ± .015	APPROVALS		USB 3.0 PLUG TYPE B			
.XXX ± .015	Ø.XXX ± .010	DRAWN	HR	DATE	SIZE	PART NO.	REV.
		CHECKED	TW	10/13/15	X	CA-USB3-AM/BM-XFT	-
		APPROVED			REF: S00087T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-USB3-AM-BM-6FT](#)