


APPROVED: _____
 DATE: _____ TITLE: _____
 CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

| Rev | AWO # | Description | Date | Appr |
|-----|-------|-----------------------|----------|-------|
| - | | RELEASED | 10/13/15 | |
| A | | ADDED 1FT PART NUMBER | 5/3/19 | AY/TW |



| PIN ASSIGNMENT | | | |
|----------------|-------|---|-------|
| P1 | | | P2 |
| 1 — | RED | — | 1 |
| 2 — | WHITE | — | 2 |
| 3 — | GREEN | — | 3 |
| 4 — | BLACK | — | 4 |
| SHELL — | BRAID | — | SHELL |

| ADAM P/N | L |
|-------------------|-----------------------------|
| CA-USB-AM/AF-1FT | 12.008"±.787" [305±20mm] |
| CA-USB-AM/AF-3FT | 36.024"±1.181" [915±30mm] |
| CA-USB-AM/AF-6FT | 72.047"±1.969" [1830±50mm] |
| CA-USB-AM/AF-10FT | 120.079"±1.969" [3050±50mm] |

SPECIFICATIONS:
Connector:
 P1= USB Connector 2.0 A Type Plug, Insulator Color: White, Overmold Color: Black, 50P PVC
 P2= USB Connector 2.0 A Type Socket, Insulator Color: White, Overmold Color: Black, 50P PVC
Cable:
 UL2725, (1P+2C)+A+B, OD: .189" [4.8mm] (28/24),Jacket Color: Black .
Electrical Test:
 All Assemblies must be 100% Tested for
 Shorts, Open, Continuity, and Physical Appearance.
Environmental:
 Lead free, RoHS compliant



| | | | | | |
|---|--|-----------------------------------|--|---|--|
| UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010 | | ADAM TECH INTERCONNECTS | | 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710 | |
| APPROVALS DRAWN HR CHECKED TW APPROVED | | DATE 10/13/15 10/13/15 | | TITLE CUSTOMER ASSEMBLY, USB 2.0 PLUG TYPE A TO USB 2.0 SOCKET TYPE A | |
| SIZE X | | PART NO. CA-USB-AM/AF-XFT | | REV. A | |
| REF: S00087T | | SCALE: NTS | | SHEET 1 OF 1 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-USB-AM-AF-10FT](#)