


6 5 4 3 2 1

APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_  
CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	
A		ADDED P/N OPTIONS	10/1/18	HR/RC1
B		ADDED P/N OPTIONS	11/20/19	AY/TW
C		ADDED P/N OPTIONS	8/28/20	AY/JL



PIN ASSIGNMENT			
P1			P2
1	—	RED	1
2	—	WHITE	2
3	—	GREEN	3
4	—	BLACK	4
S	—	BRAID	S

ADAM P/N	L
CA-USB-AM/BM-3FT	36.024"±1.181" [915±30mm]
CA-USB-AM/BM-6FT	72.047"±1.969" [1830±50mm]
CA-USB-AM/BM-10FT	120.079"±1.969" [3050±50mm]
CA-USB-AM/BM-3.3FT	39.764"±1.181" [1010±30mm]
CA-USB-AM/BM-16.4FT	197.244"±1.969" [5010±50mm]
CA-USB-AM/BM-7.5FT	90.945"±1.969" [2310±50mm]
CA-USB-AM/BM-6.5FT	78.740"±1.969" [2000±50mm]

**SPECIFICATIONS:**

**Connector:**

P1= USB Connector 2.0 A Type Plug, Insulator Color: White, Overmold Color: Black, 50P PVC

P2= USB Connector 2.0 B Type Plug, Insulator Color: White, Overmold Color: Black, 50P PVC

**Cable:**

UL2725, (1P+2C)+A+B, OD: .189" [4.8mm] (28/24),Jacket Color: Black .

**Electrical Test:**

All Assemblies must be 100% Tested for  
Shorts, Open, Continuity, and Physical Appearance.

**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	HR	10/13/15
CHECKED	TW	10/13/15
APPROVED		

**ADAM  
TECH**  
INTERCONNECTS

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
CUSTOMER ASSEMBLY, USB 2.0 PLUG TYPE A  
TO USB 2.0 PLUG TYPE B

SIZE X	PART NO. CA-USB-AM/BM-XFT	REV. C
REF: S00087T	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-USB-AM-BM-6FT](#)