


APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	
A		UPDATE DIM.	9/27/19	AY/JC



PIN ASSIGNMENT

P1		P2
1	COAX-RED-IN	1
6	COAX-RED-GND	6
2	COAX-GRN-IN	2
7	COAX-GRN-GND	7
3	COAX-BLU-IN	3
8	COAX-BLU-GND	8
4		4
5		5
10		10
11		11
12		12
13		13
14		14
15		15
S		S

ADAM P/N	L
CA-VGA-M/M-3FT	36.024"±1.181" [915±30mm]
CA-VGA-M/M-6FT	72.047"±1.969" [1830±50mm]
CA-VGA-M/M-10FT	120.079"±1.969" [3050±50mm]

SPECIFICATIONS:

Connector:

P1=P2= High Density D-Sub Connector 15P, VGA Plug,
Insulator Color: Blue, Overmold Color: Black, 50P PVC

Cable:

UL2919, 28/28-3C/9+A+D+B, OD: .315" [8mm], Jacket Color: Black <AL-Braid>

Electrical Test:

All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	HR	10/13/15
CHECKED	TW	10/13/15
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
CUSTOM ASSEMBLY, VGA PLUG TO VGA PLUG			
SIZE X	PART NO. CA-VGA-M/M-XFT	REV. A	
REF: S00087T	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-VGA-M-M-10FT](#)