





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/7/05	
A		FIXED PART NUMBER	04/24/06	BAS



SECTION C-C



# SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 3A AC/DC.

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 18

A = .100 [2.54] x No. of Positions

B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
		TITLE	
APPROVALS		DATE	
DRAWN	SS	4/7/05	
CHECKED			
APPROVED			
		SIZE	PART NO.
		X	CDH-XX
		REV.	-
REF:		SCALE: NTS	SHEET 1 OF 1

.100 [2.54] LATCHING HOUSING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CDH-08](#) [CDH-C-G-R](#) [CDH-05](#) [CDH-03](#) [CDH-07](#) [CDH-09](#) [CDH-C-B](#) [CDH-02](#) [CDH-C-SG-15-R](#) [CDH-11](#) [CDH-12](#)  
[CDH-10](#) [CDH-05-NL](#) [CDH-04](#) [CDH-06](#) [CDH-03-NL](#)