





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/7/05	
A		REVISED SPEC.	11/20/12	



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 12
A = .100 [2.54] x No. of Positions + .100 [2.54]
B = .100 [2.54] x No. of Spaces

PCB LAYOUT

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.100 [2.54] LATCHING HEADER
STRAIGHT, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXX	± .010	APPROVALS	DATE		
DRAWN	SS		4/7/05	CHECKED			
APPROVED				SIZE	PART NO.	CDR-XX-GS	REV. A
				REF:	SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CDR-02-GS](#) [CDR-03-GS](#) [CDR-04-GS](#) [CDR-05-GS](#) [CDR-08-GS](#) [CDR-07-GS](#) [CDR-12-GS](#) [CDR-09-GS](#) [CDR-10-GS](#) [CDR-06-GS](#) [CDR-11-GS](#)