




APPROVED: _____
DATE: _____ TITLE: _____

| Rev | AWO # | Description | Date | Appr |
|-----|-------|-----------------------|---------|--------|
| - | | RELEASED | 1/11/05 | |
| A | | REVISED LOW FEET DIM. | 3/20/08 | |
| B | | REDRAWN | 6/30/14 | HR/QZL |



SPECIFICATIONS:

Material:
Contact: Phosphor Bronze
Plating:
Gold flash over Nickel underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 3 Amps max
Contact resistance: 20 mohms max initial
Mechanical:
Recommended wire range: 24–28 AWG
Temperature Rating:
Operating temperature: –55°C to +105°C
Packaging:
B = Loose Cut
R = Tape and Reel
Environmental:
Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB PLUG CONTACT, 24-28 AWG

GOLD FLASH

| | | | | | |
|--|--|---|--|--------------|--|
| UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 .XX ± .020 .XXX ± .015 | | HOLE ØX ± .10 ØXX ± .015 ØXXX ± .010 | | DATE | |
| DRAWN | | SS | | 1/11/05 | |
| CHECKED | | | | | |
| APPROVED | | | | | |
| TITLE | | SIZE | | PART NO. | |
| D-SUB PLUG CONTACT, 24-28 AWG | | X | | DCP-01-X | |
| GOLD FLASH | | REF: S00087T | | SCALE: NTS | |
| | | | | SHEET 1 OF 1 | |
| | | | | REV. B | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DCP-01-R](#)