




6 5 4 3 2 1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/20	



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Electrical:

Current rating: 06~15P: 9 Amp Max (With UL1007, 16AWG)

Contact resistance: 20 mohms max

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 2,900 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.



A = .250 [6.35] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE			
DRAWN		LH	2/21/20			
CHECKED		AY1	2/21/20			
APPROVED						
TITLE			WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITH POLARIZING PEG, FEMALE PIN			
SIZE X		PART NO. DME-F-XX-S2-P-SQ			REV. -	
REF:		S00124T		SCALE:	NTS	
				SHEET	1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DME-F-09-S2-P-SQ](#) [DME-F-06-S2-P-SQ](#) [DME-F-12-S2-P-SQ](#)