







APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/26/10	
A		ADDED DIM.	10/27/17	AY/NC



RECOMMENDED PCB LAYOUT

#### SPECIFICATIONS:

##### Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contact: Phosphor Bronze, Tin plated

##### Electrical:

Voltage rating: 600 VAC

Current rating: 13 Amp (2~4P), 11 Amp (6~10P).

Dielectric withstanding voltage: 5000 VAC for 1 minute

Temperature Rating:

-55°C to +105°C

##### Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 10

A = .250 [6.35] No. of Positions + .050 [1.27]

B = .250 [6.35] No. of Spaces

C = .250 [6.35] No. of Positions + .330 [8.38]

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ±.10 Ø.X ±.10  
.XX ±.020 Ø.XX ±.015  
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	DY	10/26/10
CHECKED		
APPROVED		

## ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
WIRE TO BOARD HEADER, MALE WITH EARS  
6.35MM, RIGHT ANGLE

SIZE X	PART NO. DME-M-XX-RA-E	REV. -
REF: S00123T	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DME-M-04-RA-E](#) [DME-M-06-RA-E](#) [DME-M-05-RA-E](#) [DME-M-03-RA-E](#) [DME-M-02-RA-E](#) [DME-M-08-RA-E](#)