





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/05/08	
A		REVISED OPERATING TEMP.	2/10/10	
B		REVISED SPEC	9/9/11	



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Contacts: Brass, Tin plated

Electrical:

Operating voltage: 600 VAC max

Current rating: 13 Amps max.

Insulation resistance: 1000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 5000 VAC for 1 minute

Mechanical:

Temperature Rating:

-55°C to +105°C

Environmental:

Lead free, RoHS compliant.



Poles: 02 thru 10

A = .250 [6.35] X No. of Positions + .050 [1.27]

B = .250 [6.35] X No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	9/05/08
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH
WITHOUT POLARIZING, SINGLE ROW TYPE

SIZE X	PART NO. DME-XX-S-S	REV. B
REF: S00004T		SCALE: NTS
		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DME-05-S-S](#) [DME-06-S-S](#) [DME-02-S-S](#) [DME-03-S-S](#) [DME-04-S-S](#) [DME-08-S-S](#)